

Vacuum pump

EVE-WR 45 AC3

Part no.:10.03.05.00015

<https://www.schmalz.com/10.03.05.00015>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Water-Ring Pumps EVE-WR > EVE-WR 45 AC3

Water-ring pump, wear-free, robust, requires little maintenance



Suction rate (50 Hz): 45 m³/h

Current type: three-phase current

Sound level at 50 Hz: 67 dB(A)


Voltage at 50Hz: 200-240V or 345-420V

Rated power 50 Hz: 1.2 kW

Rated power 60 Hz: 1.2 kW

Weight: 55 kg

Design Data



Attribute	Value
B	572 mm
d	14 mm
D2	50 mm
H	436 mm
H1	553 mm
L	744 mm
L2	85 mm
X1	450 mm
Y1	495 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	45 m ³ /h
Voltage at 50Hz	200-240V or 345-420V
Voltage at 60Hz	200-275V o. 345-480V
Rated power 50 Hz	1.20 kW
Rated power 60 Hz	1.20 kW
Sound level at 50 Hz	67 dB(A)
Weight	55 kg
Protection type IP	IP 54

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum pump

EVE-WR 45 AC3

Part no.:10.03.05.00015

<https://www.schmalz.com/10.03.05.00015>

Current type

AC3

Accessories



MSS-K 4-6.3A

Part no.:10.04.04.00121

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de