

Solenoid valve

EMV 3 24V-DC 2/2 NC

Part no...:10.05.01.00066

<https://www.schmalz.com/10.05.01.00066>




Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMV > EMV 3 24V-DC 2/2 NC

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 3 mm
Voltage DC: 24V - DC
Function: 2/2-way valve
Control valve: Normally closed
Connecting thread: G1/4"-F
Pressure range (operating pressure): -1.00 ... 9.00 bar
Power consumption DC: 5 W

Design Data



Attribute	Value
B1	61.50 mm
B2	47 mm
G1	G1/4"-F
G5	M3-F
H	22 mm
H1	60 mm
L	42 mm
LG1	12 mm
LG5	5 mm

Technical Data

Attribute	Value
Nominal size	3 mm
Control valve	Normally closed
Nominal flow rate	33.30 l/min
Nominal flow rate	2 m³/h
Power consumption DC	5 W
Voltage DC	24V - DC
Closing time	20 ms
Weight	0.20 kg

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de



Solenoid valve

EMV 3 24V-DC 2/2 NC

Part no...:10.05.01.00066

<https://www.schmalz.com/10.05.01.00066>

Product family

EMV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de