

Solenoid valve

EMV 20 230V-AC 3/2 NO


Part no.:10.05.01.00075

<https://www.schmalz.com/10.05.01.00075>




Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMV > EMV 20 230V-AC 3/2 NO

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 20 mm
Voltage DC: 230V - AC
Function: 3/2-way valve
Control valve: Normally open
Connecting thread: G1"-F
Pressure range (operating pressure): bar
Power consumption DC: 40.8 W

Design Data



Attribute	Value
d	8.50 mm
D	80 mm
G1	G1"-F
G2	G1"-F
G3	G1"-F
H	137 mm
H1	172 mm
L	247 mm
L1	245 mm
X1	148 mm
Y1	45 mm

Technical Data

Attribute	Value
Nominal size	20 mm
Control valve	Normally open
Nominal flow rate	883.30 l/min
Nominal flow rate	53 m³/h
Power consumption DC	40.80 W
Voltage DC	230V - AC

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Solenoid valve

EMV 20 230V-AC 3/2 NO

Part no.:10.05.01.00075

<https://www.schmalz.com/10.05.01.00075>

Closing time	100 ms
Weight	6.38 kg
Product family	EMV

Accessories



FAS 80x38 G1-AG EMVP

Part no.:10.05.01.00063

External diameter D: 80 mm

Length L: 38 mm

Thread G1: G1"-M

Construction use: Solenoid valve

Spare parts



FAS 80x38 G1-AG EMVP

Part no.:10.05.01.00063

External diameter D: 80 mm

Length L: 38 mm

Thread G1: G1"-M

Construction use: Solenoid valve

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de