

Solenoid valve

EMVP 50 24V-DC 3/2 NO

Part no.:10.05.02.00069

<https://www.schmalz.com/10.05.02.00069>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVP > EMVP 50 24V-DC 3/2 NO

Solenoid valve EMVP for vacuum, pneumatic pilot control



Nominal size: 50 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open


Connecting thread: G2"-F

Pressure range (operating pressure): bar

Nominal flow rate: 310 m³/h

Weight: 1.36 kg

Design Data



Attribute	Value
B	114 mm
B1	151 mm
B2	105.50 mm
D	80 mm
G1	G2"-F
G2	G2"-F
G3	G1-1/4"-F
G4	G1/8"-F
G5	G3/8"-F
H	142 mm
L	225 mm
L1	260 mm
X1	49 mm

Technical Data

Attribute	Value
Nominal size	50 mm
Nominal flow rate	310 m³/h
Control valve	Normally open
Nominal flow rate	5,166.70 l/min

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Solenoid valve


EMVP 50 24V-DC 3/2 NO

Part no...:10.05.02.00069

<https://www.schmalz.com/10.05.02.00069>

Power consumption DC	5 W
Voltage DC	24V - DC
Closing time	500 ms
Weight	1.36 kg
Product family	EMVP

Accessories



FAS 80x32 G1-1/4-AG EMVP-25+50

Part no...:10.05.01.00064

External diameter D: 80 mm

Length L: 32 mm

Thread G1: G1-1/4"-M

Construction use: Solenoid valve

Size: 25+50

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de