

Dust filter (with pressure monitor)

STF-D 75 P 8.0 F SSD

Part no.:10.07.01.00265

<https://www.schmalz.com/10.07.01.00265>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF-D 75 P 8.0 F SSD

Dust filter (with pressure monitor)



Connection: Ø75mm

Shape: Piclon housing


Nominal flow rate: 480 m³/h

Filter pore size: 3 µm

Add. function: Filter monitoring

Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	280 mm
B2	148 mm
d	8.50 mm
D	228 mm
D1	248 mm
D2	75 mm
D3	75 mm
H	260 mm
L	415 mm
L1	774 mm
L2	359 mm
X1	237 mm

Technical Data

Attribute	Value
Connection	Ø75mm
Nominal flow rate	480 m³/h
Nominal flow rate	8000 l/min
Max. vacuum	-500 mbar
Filter pore size	3 µm
Weight	2.60 kg

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Dust filter (with pressure monitor)

STF-D 75 P 8.0 F SSD

Part no.:10.07.01.00265

<https://www.schmalz.com/10.07.01.00265>

Product family

VF

Spare parts



FILT-EINS 3 159x376 STF-Picl-8

Part no.:10.07.01.00079

Filter pore size: 3 µm


External diameter D: 159.2 mm

Length L: 376 mm

Construction use: Dust filter STF

Size: Picl-8

Type: 480m³/h



DDW 10...50 250V-AC/6

Part no.:21.01.06.00011



SSD 76.5-84 ST-VZ

Part no.:10.07.10.00037

Clamping range: 76.5 ... 84.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Dust filter (with pressure monitor)

STF-D 75 P 8.0 F SSD

Part no...:10.07.01.00265

<https://www.schmalz.com/10.07.01.00265>



FILT-EINS 3 159x376 STF-Picl-8

Part no...:10.07.01.00079

Filter pore size: 3 µm

External diameter D: 159.2 mm

Length L: 376 mm

Construction use: Dust filter STF

Size: Picl-8

Type: 480m³/h