

Flexolink HD

FLK-HD G3/8-AG

Part no.: 10.07.06.00235

<https://www.schmalz.com/10.07.06.00235>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > FLK-HD G3/8-AG

Flexible, reinforced suction cup mounting FLK-HD for adaption to sloping surfaces




Thread G1: G3/8"-M

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

Design Data



Attribute	Value
L	31.60 mm
D	69 mm
dn	9 mm
d	6.40 mm
G1	G3/8"-M
LG1	27 mm
G2	M6-M
LG2	10.50 mm
SW1	17 mm
SW2	5 mm
Dmk	58.30 mm
W	7.50 °
Fitting length	31.60 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de