

Compressed-air hose

VSL 15-9 PVC-G KL-TR

Part no.:10.07.09.00005

<https://www.schmalz.com/10.07.09.00005>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices VacuMaster > Spare and Wear Parts VacuMaster Eco > VSL 15-9 PVC-G KL-TR

Compressed-air hose



External diameter D: 15 mm

Internal diameter d: 9 mm


Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

Design Data



Attribute	Value
d	9 mm
D	15 mm

Technical Data

Attribute	Value
Hose type	15-9
Pressure range (operating pressure)	bar
Operating temperature	°C
Length max.	50 m
Weight/Meter	144 g/m
Weight/Meter	0.14 kg/m
Material hose	PVC with tissue
Product family	VSL

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Compressed-air hose

VSL 15-9 PVC-G KL-TR

Part no.:10.07.09.00005

<https://www.schmalz.com/10.07.09.00005>

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 10-16 ST-VZ

Part no.:10.07.10.00001

Clamping range: 10.0 ... 16.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



ST G1/2-AG 9 MS-V

Part no.:10.08.03.00161

Thread G1: G1/2"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 6.1 mm

Nominal diameter dn: 7.5 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Compressed-air hose

VSL 15-9 PVC-G KL-TR

Part no...:10.07.09.00005

<https://www.schmalz.com/10.07.09.00005>



ST G1/4-AG 9 MS-V

Part no...:10.08.03.00157

Thread G1: G1/4"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 7.5 mm



ST G1/8-AG 9 MS-V

Part no...:10.08.03.00155

Thread G1: G1/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4 mm



ST G3/8-AG 9 MS-V

Part no...:10.08.03.00159

Thread G1: G3/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 6 mm

Nominal diameter dn: 7.4 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de