

## Vacuum hose (meter)

VSL 41-35 PVC-PS GR

Part no.:10.07.09.00010

<https://www.schmalz.com/10.07.09.00010>

Home > Vacuum Lifters and Crane Systems > Vacuum Tube Lifters Jumbo > Spare Parts Vacuum Tube Lifters Jumbo > Spare and Wear Parts Vacuum Tube Lifters JumboErgo / Jumbo Sprint > VSL 41-35 PVC-PS GR

### Hose for vacuum and compressed-air systems



External diameter D: 41 mm

Internal diameter d: 35 mm

Length max.: 50 m

Material hose: PVC with PVC-spiral

Bending radius min.: 65 mm

Pressure range (operating pressure): -0.50 ... 0.50 bar

Operating temperature: -20 ... 70 °C

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 35 mm |
| D         | 41 mm |

### Technical Data

| Attribute                           | Value               |
|-------------------------------------|---------------------|
| Hose type                           | 41-35               |
| Pressure range (operating pressure) | -0.50 ... 0.50 bar  |
| Operating temperature               | -20 ... 70 °C       |
| Bending radius min.                 | 65 mm               |
| Length max.                         | 50 m                |
| Weight/Meter                        | 320 g/m             |
| Weight/Meter                        | 0.32 kg/m           |
| Material hose                       | PVC with PVC-spiral |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Vacuum hose (meter)

VSL 41-35 PVC-PS GR

Part no.:10.07.09.00010

<https://www.schmalz.com/10.07.09.00010>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

### Accessories



#### SSD 35-40 ST-VZ

Part no.:10.07.10.00018

Clamping range: 35.0 ... 40.0 mm

Material: Steel

Surface: galvanised



#### SSD 37-42 ST-VZ

Part no.:10.07.10.00019

Clamping range: 37.0 ... 42.0 mm

Material: Steel

Surface: galvanised

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)