

Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 14-11 PU MI-TR

Hose for vacuum and compressed-air systems



External diameter D: 14 mm

Internal diameter d: 11 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 100 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Design Data



Attribute	Value
d	11 mm
D	14 mm

Technical Data

Attribute	Value
Hose type	14-11
Pressure range (operating pressure)	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Bending radius min.	100 mm
Length max.	50 m
Weight/Meter	69 g/m
Weight/Meter	0.07 kg/m
Material hose	PU

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



SSB 10-16 ST-VZ

Part no.:10.07.10.00001

Clamping range: 10.0 ... 16.0 mm

Material: Steel

Surface: galvanised



STV-GE G1/2-AG 14

Part no.:10.08.02.00300

Thread G1: G1/2"-M

Hose diameter: 14 mm

Material: Brass

Operating temperature: °C

External diameter D: 21.5 mm

Length L: 25 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>



STV-GE G3/8-AG 14

Part no.:10.08.02.00211

Thread G1: G3/8"-M

Hose diameter: 14 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 21.5 mm

Length L: 30.5 mm



SVB-T 14

Part no.:10.09.02.00046

Hose diameter: 14 mm

Material: Brass

Operating temperature: °C

Length L: 72 mm