

Vacuum hose (meter)

VSL 27-20 PU-DS-AS TR

Part no.:10.07.09.00047

<https://www.schmalz.com/10.07.09.00047>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 27-20 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 27 mm

Internal diameter d: 20 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 17 mm

Pressure range (operating pressure): -1.00 ... 4.72 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	20 mm
D	27 mm

Technical Data

Attribute	Value
Hose type	27-20
Pressure range (operating pressure)	-1.00 ... 4.72 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	17 mm
Length max.	20 m
Weight/Meter	230 g/m
Weight/Meter	0.23 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 27-20 PU-DS-AS TR

Part no.:10.07.09.00047

<https://www.schmalz.com/10.07.09.00047>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 24-27 ST-VZ

Part no.:10.07.10.00086

Clamping range: 24.0 ... 27.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de