

Hose clamp

SSD 24-27 ST-VZ

Part no.: 10.07.10.00086

<https://www.schmalz.com/10.07.10.00086>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 24-27 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 24.0 ... 27.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	24 mm
d2	27 mm
L	12 mm

Technical Data

Attribute	Value
Clamping range	24.0 ... 27.0 mm
Material	Steel
Weight	13.50 g
Product family	SSB / SSD

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de


Hose clamp

SSD 24-27 ST-VZ

Part no.:10.07.10.00086

<https://www.schmalz.com/10.07.10.00086>

Accessories



VSL 27-20 PU-DS-AS TR

Part no.:10.07.09.00047

External diameter D: 27 mm

Internal diameter d: 20 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 17 mm

Pressure range (operating pressure): -1.00 ... 4.72 bar

Operating temperature: -40 ... 90 °C