

Hose clamp

SSD 28-32 ST-VZ

Part no.: 10.07.10.00087

<https://www.schmalz.com/10.07.10.00087>

Home > Vacuum Lifters and Crane Systems > Vacuum Tube Lifters Jumbo > Spare Parts Vacuum Tube Lifters Jumbo > Spare and Wear Parts Vacuum Tube Lifters JumboFlex > SSD 28-32 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 28.0 ... 32.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	28 mm
d2	32 mm
L	12 mm

Technical Data

Attribute	Value
Clamping range	28.0 ... 32.0 mm
Material	Steel
Weight	14.50 g
Product family	SSB / SSD

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de


Hose clamp

SSD 28-32 ST-VZ

Part no.:10.07.10.00087

<https://www.schmalz.com/10.07.10.00087>

Accessories



VSL 32-25 PU-DS-AS TR

Part no.:10.07.09.00051

External diameter D: 32 mm

Internal diameter d: 25 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 20 mm

Pressure range (operating pressure): -1.00 ... 3.86 bar

Operating temperature: -40 ... 90 °C