

Hose sleeve

ST G3/4-AG 19 MS-V

Part no.:10.08.03.00165

<https://www.schmalz.com/10.08.03.00165>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G3/4-AG 19 MS-V

Hose sleeve



Thread G1: G3/4"-M

Hose diameter (rec.) d: 19 mm


Material: Brass

Surface: nickel plated

Length L: 7.8 mm

Nominal diameter dn: 16 mm

Design Data



Attribute	Value
dn	16 mm
D	19 mm
G1	G3/4"-M
L	7.80 mm
L1	60 mm
LG1	15.80 mm
SW1	32 mm

Technical Data

Attribute	Value
Material	Brass
Weight	116 g

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Hose sleeve

ST G3/4-AG 19 MS-V

Part no...:10.08.03.00165

<https://www.schmalz.com/10.08.03.00165>



VSL 26-19 PVC-DS KL-TR

Part no...:10.07.09.00007

External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 |
customercenter@schmalz.de