

Hose sleeve

ST G1-AG 32 MS-V

Part no.:10.08.03.00168

<https://www.schmalz.com/10.08.03.00168>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1-AG 32 MS-V

Hose sleeve



Thread G1: G1"-M

Hose diameter (rec.) d: 32 mm


Material: Brass

Surface: nickel plated

Length L: 10.5 mm

Nominal diameter dn: 26 mm

Design Data



Attribute	Value
dn	26 mm
D	32 mm
G1	G1"-M
L	10.50 mm
L1	62 mm
LG1	16 mm
SW1	36 mm

Technical Data

Attribute	Value
Material	Brass
Weight	176 g

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Hose sleeve

ST G1-AG 32 MS-V

Part no.:10.08.03.00168

<https://www.schmalz.com/10.08.03.00168>



VSL 41-32 PVC-DS KL-TR

Part no.:10.07.09.00008

External diameter D: 41 mm

Internal diameter d: 32 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C



DR G1 39/34x2 PA

Part no.:10.07.08.00025

for: G1

External diameter D: 39 mm

Internal diameter d: 34 mm

Material: Polyamide