

Plug union, T

STV-T G1/4-AG 12

Part no.:10.09.02.00045

<https://www.schmalz.com/10.09.02.00045>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-T G1/4-AG 12

Push-in Fitting, T



Thread G1: G1/4"-M


Hose diameter: 12 mm

Material: Brass

Operating temperature: °C

Length L: 69 mm

Design Data



Attribute	Value
d	12 mm
G1	G1/4"-M
dn	8.40 mm
D1	19.60 mm
H	16.80 mm
H1	26.60 mm
L	69 mm
LG1	7.60 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 12 d = 9
Hose type	12-9
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	113.40 g
Product family	STV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Plug union, T

STV-T G1/4-AG 12

Part no.:10.09.02.00045

<https://www.schmalz.com/10.09.02.00045>

Accessories



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de