

## Quick change suction cup

SQC-C-RU-80x102-NBR

Part no.:10.01.18.01037

<https://www.schmalz.com/10.01.18.01037>

Home > Vacuum Clamping Technology > Clamping Equipment for Glass Processing > Quick-Change Systems for Bystronic Machines > Schmalz Quick-Change SQC > SQC-C-RU-80x102-NBR

### Quick Change Suction Cup



External diameter D: 80 mm

Height H: 102 mm

Construction use: Quick-change system

Dimensions (LxB): Diameter 80 mm


Material: Aluminum

Material: ED

Material hardness [Shore A]: 85 Shore A

Sealing material: Perbunan

### Design Data



| Attribute | Value     |
|-----------|-----------|
| D         | 80 mm     |
| H         | 102 mm    |
| H1        | 119.80 mm |

### Spare parts

#### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Quick change suction cup

SQC-C-RU-80x102-NBR

Part no...:10.01.18.01037

<https://www.schmalz.com/10.01.18.01037>



**V-RING 63x11 V-070 NBR**

Part no...:10.07.08.00554

External diameter D: 75 mm

Type: V-070