

Adapter-Plate


ISAP-K2 200x200x28

Part no...:10.01.14.00029

<https://www.schmalz.com/10.01.14.00029>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for 2-Circuit Systems > Adapter-Plates ISAP-K2 > ISAP-K2 200x200x28

Adapter-Plate Innospann for Schmalz 2-circuit console




Length L: 200 mm

Width B: 200 mm

Height H: 28 mm

Design Data



Attribute	Value
B	200 mm
H	28 mm
L	200 mm

Technical Data

Attribute	Value
Weight	2.95 kg

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Adapter-Plate

ISAP-K2 200x200x28

Part no...:10.01.14.00029

<https://www.schmalz.com/10.01.14.00029>



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm

Contact Schmalz


J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Adapter-Plate

ISAP-K2 200x200x28

Part no...:10.01.14.00029

<https://www.schmalz.com/10.01.14.00029>



ISMB 80x80x42

Part no...:10.01.15.00078

Dimensions (LxB): 80x80

Basic area: 80 x 80 mm

Length L: 80 mm

Width B: 80 mm

Height H: 42 mm

Spare parts



ISMST 19-7 4ISMST

Part no...:10.01.14.00847

External diameter D: 7 mm

Height H: 11.5 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de