

Quad-Base

ISQB 175x175x22

Part no.:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISQB 175x175x22

Quad-Base for Steelplate and Adapterplate



Dimensions (LxB): 175x175


Basic area: 175 x 175 mm

Length L: 175 mm

Width B: 175 mm

Height H: 22 mm

Design Data



Attribute	Value
B	175 mm
d	60 mm
H	22 mm
L	175 mm

Technical Data

Attribute	Value
Weight	1.02 kg

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Quad-Base

ISQB 175x175x22

Part no...:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



ABDK 80x4 ISQB

Part no...:10.01.15.00083

External diameter D: 80 mm

Height H: 4 mm



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Quad-Base

ISQB 175x175x22

Part no...:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm



ISZR-V 80x15

Part no...:10.01.15.00052

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 15 mm



ISZR-V 80x20

Part no...:10.01.15.00053

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 20 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Quad-Base

ISQB 175x175x22

Part no.:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



ISZR-V 80x45

Part no.:10.01.15.00054

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 45 mm

Spare parts



DI-SCHN 8 MOS EPDM-20

Part no.:10.07.04.00002

External diameter D: 8 mm

Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de