

Vacuum hose (meter)

VSL 33-25 PVC-DS KL-TR

Part no.:10.07.09.00041

<https://www.schmalz.com/10.07.09.00041>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 33-25 PVC-DS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 33 mm

Internal diameter d: 25 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 95 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C

Design Data



Attribute	Value
d	25 mm
D	33 mm

Technical Data

Attribute	Value
Hose type	33-25
Pressure range (operating pressure)	-0.85 ... 4.00 bar
Operating temperature	-15 ... 65 °C
Bending radius min.	95 mm
Length max.	50 m
Weight/Meter	510 g/m
Weight/Meter	0.51 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 33-25 PVC-DS KL-TR

Part no.:10.07.09.00041


<https://www.schmalz.com/10.07.09.00041>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 23-35 ST-VZ

Part no.:10.07.10.00161

Clamping range: 23.0 ... 35.0 mm

Material: Steel

Surface: galvanised



SSB 32-50 ST-VZ

Part no.:10.07.10.00004

Clamping range: 32.0 ... 50.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 33-25 PVC-DS KL-TR

Part no...:10.07.09.00041

<https://www.schmalz.com/10.07.09.00041>



ST G1-AG 25 MS-V

Part no...:10.08.03.00167

Thread G1: G1"-M

Hose diameter (rec.) d: 25 mm

Material: Brass

Surface: nickel plated

Length L: 10.1 mm

Nominal diameter dn: 22 mm



ST G3/4-AG 25 MS-V

Part no...:10.08.03.00166

Thread G1: G3/4"-M

Hose diameter (rec.) d: 25 mm

Material: Brass

Surface: nickel plated

Length L: 8.5 mm

Nominal diameter dn: 18.5 mm