

Vacuum block Innospann

ISBL-HD 80x40x97

Part no...:10.01.15.00658

<https://www.schmalz.com/10.01.15.00658>




Home > Vacuum Clamping Technology > Clamping Equipment for Metal and Plastic Processing > Modular Clamping System MPL-ISST-SFM for Metal and Plastics Machining > Innospann Steel-Plate ISST-MPL and Vacuum Blocks ISBL > ISBL-HD 80x40x97

Innospann vacuum block for Steelplate and Adapterplate



Length L: 80 mm
Width B: 40 mm
Dimensions (LxB): 80 x 40
Basic area: 80 x 80 mm
Height H: 97 mm

Design Data



Attribute	Value
B	40 mm
B1	80 mm
H	97 mm
L	80 mm
L1	80 mm

Spare parts

Vacuum block Innospann

ISBL-HD 80x40x97

Part no.:10.01.15.00658

<https://www.schmalz.com/10.01.15.00658>



ISDR 81x43x12 Cup 2 NBR-50

Part no.:10.01.15.00418

Length L: 81 mm

Width B: 43 mm

Height H: 12 mm



ISDR 81x81x12 Cup 1 NBR-50

Part no.:10.01.15.00158

Length L: 81 mm

Width B: 81 mm

Height H: 12 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de