

Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no...:10.01.12.02673

<https://www.schmalz.com/10.01.12.02673>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block
VCBL-R > VCBL-R 160x96x45 40x40 TV

Vacuum block for grid tables



Dimensions (LxB): 160 x 96

Length L: 160 mm

Width B: 80 mm


Height H: 45 mm

Grid: 40x40

Recommended slot width x slot depth [mm]: 6,5x6,5 / 7,5x7,5 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	80 mm
H	45 mm
H2	22 mm
L	160 mm
L1	160 mm

Technical Data

Attribute	Value
Grid	40x40
Weight	0.66 kg

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no...:10.01.12.02673

<https://www.schmalz.com/10.01.12.02673>



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



ERS VCBL-R Winkel

Part no...:10.01.12.02691



ERS VCBL-R

Part no...:10.01.12.02693

Contact Schmalz


J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no...:10.01.12.02673

<https://www.schmalz.com/10.01.12.02673>



DR 141/149x6 MOS NK-20

Part no...:10.01.12.02902

External diameter D: 141 mm

Internal diameter d: 149 mm

Length L: 6 mm

Width B: 4 mm

Height H: 6 mm

Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de