

Cup

ISCUP Cup 2 80x40x30 TV

Part no...:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 2 80x40x30 TV

Suction cup for Innospann



Dimensions (LxB): 80 x 40


Length L: 80 mm

Width B: 40 mm

Height H: 30 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	40 mm
d	60 mm
H	30 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.10 kg

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Cup

ISCUP Cup 2 80x40x30 TV

Part no...:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062

Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x43x12 Cup 2 NK-50

Part no...:10.01.15.00021

Width B: 43 mm

Height H: 12 mm

Length L: 81 mm

Suction cup material: Natural rubber NK-50

Type: Cup 2



ISRPL 66x26x8.5 NK-45 d12

Part no...:10.01.15.00344

Width B: 26 mm

Internal diameter d: 12 mm

Height H: 8.5 mm

Length L: 66 mm

Suction cup material: Natural rubber NK-45

Type: Cup 2

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Cup

ISCUP Cup 2 80x40x30 TV

Part no...:10.01.15.00305

<https://www.schmalz.com/10.01.15.00305>



O-RING 48x2 CR-70

Part no...:10.07.08.00468



TV D11 4.3

Part no...:10.01.15.00347

External diameter D: 11 mm

Spring stroke Z: 4.3 mm

Length L: 24 mm