

Mono-Base

ISMB 80x80x8

Part no.: 10.01.15.00188

<https://www.schmalz.com/10.01.15.00188>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISMB 80x80x8

Mono-Base for Steelplate and Adapterplate



Dimensions (LxB): 80x80


Basic area: 80 x 80 mm

Length L: 80 mm

Width B: 80 mm

Height H: 8 mm

Design Data



Attribute	Value
B	80 mm
d	60 mm
H	8 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.04 kg

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mono-Base

ISMB 80x80x8

Part no...:10.01.15.00188

<https://www.schmalz.com/10.01.15.00188>



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de