

Cup

ISCUP Cup 3 80x28x16

Part no...:10.01.15.00211

<https://www.schmalz.com/10.01.15.00211>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 3 80x28x16

Suction cup for Innospann




Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 16 mm

Design Data



Attribute	Value
B	28 mm
d	60 mm
H	16 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.06 kg

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Cup

ISCUP Cup 3 80x28x16

Part no...:10.01.15.00211

<https://www.schmalz.com/10.01.15.00211>



O-RING 48x2 CR-70

Part no...:10.07.08.00468



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062


Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x31x12 Cup 3 NK-50

Part no...:10.01.15.00022

Width B: 31 mm

Height H: 12 mm

Length L: 81 mm

Suction cup material: Natural rubber NK-50

Type: Cup 3

Cup

ISCUP Cup 3 80x28x16

Part no...:10.01.15.00211

<https://www.schmalz.com/10.01.15.00211>



ISRPL 66x14x8.5

Part no...:10.01.15.00019

Width B: 14 mm

Height H: 8.5 mm

Length L: 66 mm

Type: Cup 3