

## Quad-Base

ISQB 175x175x22

Part no.:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISQB 175x175x22

### Quad-Base for Steelplate and Adapterplate



Dimensions (LxB): 175x175


Basic area: 175 x 175 mm

Length L: 175 mm

Width B: 175 mm

Height H: 22 mm

### Design Data



| Attribute | Value  |
|-----------|--------|
| B         | 175 mm |
| d         | 60 mm  |
| H         | 22 mm  |
| L         | 175 mm |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 1.02 kg |

### Accessories

#### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Quad-Base

ISQB 175x175x22

Part no...:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



### ABDK 80x4 ISQB

Part no...:10.01.15.00083

External diameter D: 80 mm

Height H: 4 mm



### ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



### ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Quad-Base

ISQB 175x175x22

Part no...:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



### ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm



### ISZR-V 80x15

Part no...:10.01.15.00052

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 15 mm



### ISZR-V 80x20

Part no...:10.01.15.00053

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 20 mm

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Quad-Base

ISQB 175x175x22

Part no.:10.01.15.00001

<https://www.schmalz.com/10.01.15.00001>



### ISZR-V 80x45

Part no.:10.01.15.00054

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 45 mm

## Spare parts



### DI-SCHN 8 MOS EPDM-20

Part no.:10.07.04.00002

External diameter D: 8 mm

Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)