

Hose sleeve

ST G3/8-AG 9 MS-V

Part no.:10.08.03.00159

<https://www.schmalz.com/10.08.03.00159>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G3/8-AG 9 MS-V

Hose sleeve



Thread G1: G3/8"-M

Hose diameter (rec.) d: 9 mm


Material: Brass

Surface: nickel plated

Length L: 6 mm

Nominal diameter dn: 7.4 mm

Design Data



Attribute	Value
dn	7.40 mm
D	8.50 mm
G1	G3/8"-M
L	6 mm
L1	43 mm
LG1	10 mm
SW1	19 mm

Technical Data

Attribute	Value
Material	Brass
Weight	31 g

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Hose sleeve

ST G3/8-AG 9 MS-V

Part no.:10.08.03.00159

<https://www.schmalz.com/10.08.03.00159>



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



VSL 15-9 PVC-G KL-TR

Part no.:10.07.09.00005

External diameter D: 15 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de