

## Hose sleeve


ST G3/4-AG 13 MS-V

Part no.:10.08.03.00164

<https://www.schmalz.com/10.08.03.00164>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G3/4-AG 13 MS-V

### Hose sleeve



Thread G1: G3/4"-M

Hose diameter (rec.) d: 13 mm


Material: Brass

Surface: nickel plated

Length L: 8 mm

Nominal diameter dn: 10.4 mm

### Design Data



| Attribute | Value    |
|-----------|----------|
| dn        | 10.40 mm |
| D         | 13.90 mm |
| G1        | G3/4"-M  |
| L         | 8 mm     |
| L1        | 60 mm    |
| LG1       | 16 mm    |
| SW1       | 32 mm    |

### Technical Data

| Attribute | Value |
|-----------|-------|
| Material  | Brass |
| Weight    | 116 g |

### Accessories

#### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Hose sleeve

ST G3/4-AG 13 MS-V

Part no.:10.08.03.00164

<https://www.schmalz.com/10.08.03.00164>



### VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

External diameter D: 19 mm

Internal diameter d: 13 mm


Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C



### VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

External diameter D: 21 mm

Internal diameter d: 12 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)