

Hose clamp

SSD 37-42 ST-VZ

Part no.:10.07.10.00019

<https://www.schmalz.com/10.07.10.00019>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 37-42 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 37.0 ... 42.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	37 mm
d2	42 mm
L	13 mm

Technical Data

Attribute	Value
Clamping range	37.0 ... 42.0 mm
Material	Steel
Weight	17 g
Product family	SSB / SSD

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Hose clamp

SSD 37-42 ST-VZ

Part no.:10.07.10.00019

<https://www.schmalz.com/10.07.10.00019>

Accessories



VSL 41-35 PVC-PS GR

Part no.:10.07.09.00010

External diameter D: 41 mm

Internal diameter d: 35 mm


Length max.: 50 m

Material hose: PVC with PVC-spiral

Bending radius min.: 65 mm

Pressure range (operating pressure): -0.50 ... 0.50 bar

Operating temperature: -20 ... 70 °C



VSL 42-32 PU-DS-AS TR

Part no.:10.07.09.00036

External diameter D: 42 mm

Internal diameter d: 32 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 25 mm

Pressure range (operating pressure): -1.00 ... 3.77 bar

Operating temperature: -40 ... 90 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de