

Plug union, straight

STVI-GE G1/4-IG 6

Part no.:10.08.02.00153

<https://www.schmalz.com/10.08.02.00153>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STVI-GE G1/4-IG 6

Push-in Fitting, straight



Thread G1: G1/4"-F

Hose diameter: 6 mm


Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.5 mm

Length L: 30.5 mm

Design Data



Attribute	Value
D	11.50 mm
d	6 mm
G1	G1/4"-F
L	30.50 mm
L2	12 mm
LG1	12 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 6 d = 4
Hose type	6-4
Material	Brass
Pressure range (operating pressure)	0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	27 g
Product family	STV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de


Plug union, straight

STVI-GE G1/4-IG 6

Part no.:10.08.02.00153

<https://www.schmalz.com/10.08.02.00153>

Accessories



VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de