

Plug union, elbow

STV-W G1/8-AG 10

Part no.:10.08.02.00306

<https://www.schmalz.com/10.08.02.00306>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/8-AG 10

Push-in Fitting, swivelling elbow



Thread G1: G1/8"-M


Hose diameter: 10 mm

Material: Plastics

Operating temperature: 0 ... 60 °C

Length L: 26.5 mm

Design Data



Attribute	Value
d	10 mm
G1	G1/8"-M
dn	6 mm
D1	19 mm
H	16.50 mm
H1	26 mm
L	26.50 mm
L1	34.50 mm
LG1	5 mm
SW1	16 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Plastics
Pressure range (operating pressure)	1.00 ... 10.00 bar
Operating temperature	0 ... 60 °C
Weight	28 g
Product family	STV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Plug union, elbow

STV-W G1/8-AG 10

Part no.:10.08.02.00306

<https://www.schmalz.com/10.08.02.00306>
