

Plug union, elbow

STV-W G1/8-AG 4

Part no.:10.08.03.00231

<https://www.schmalz.com/10.08.03.00231>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/8-AG 4

Push-in Fitting, swivelling elbow



Thread G1: G1/8"-M


Hose diameter: 4 mm

Material: Plastics

Operating temperature: 0 ... 60 °C

Length L: 18.5 mm

Design Data



Attribute	Value
d	4 mm
G1	G1/8"-M
dn	2 mm
D1	12 mm
H	9.50 mm
H1	15.50 mm
L	18.50 mm
L1	24.80 mm
LG1	5 mm
SW1	13 mm

Technical Data

Attribute	Value
Hose type	Hose D = 4 d = 2
Hose type	4-2
Material	Plastics
Pressure range (operating pressure)	0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Weight	12.30 g
Product family	STV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Plug union, elbow

STV-W G1/8-AG 4

Part no...:10.08.03.00231

<https://www.schmalz.com/10.08.03.00231>
