

## Plug union, elbow

STV-W G1/4-AG 4

Part no.:10.08.03.00232

<https://www.schmalz.com/10.08.03.00232>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/4-AG 4

### Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 4 mm

Material: Plastics

Operating temperature: 0 ... 60 °C

Length L: 18.5 mm

### Design Data



| Attribute | Value    |
|-----------|----------|
| d         | 4 mm     |
| G1        | G1/4"-M  |
| dn        | 2 mm     |
| D1        | 12 mm    |
| H         | 9.50 mm  |
| H1        | 15.50 mm |
| L         | 18.50 mm |
| L1        | 26.30 mm |
| LG1       | 6 mm     |
| SW1       | 16 mm    |

### Technical Data

| Attribute                           | Value              |
|-------------------------------------|--------------------|
| Hose type                           | Hose D = 4 d = 2   |
| Hose type                           | 4-2                |
| Material                            | Plastics           |
| Pressure range (operating pressure) | 0.95 ... 10.00 bar |
| Operating temperature               | 0 ... 60 °C        |
| Weight                              | 17.10 g            |
| Product family                      | STV                |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Plug union, elbow

STV-W G1/4-AG 4

Part no...:10.08.03.00232

<https://www.schmalz.com/10.08.03.00232>

---