

Sealing plug

VRS-STECH 12x16.5

Part no.:10.08.06.00041

<https://www.schmalz.com/10.08.06.00041>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > VRS-STECH 12x16.5

Sealing plug




Operating temperature: 0 ... 60 °C

External diameter D: 12 mm

Length L: 16.5 mm

Design Data



Attribute	Value
D	12 mm
D1	13.50 mm
L	16.50 mm
L1	44 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	0 ... 60 °C
Weight	3.30 g
Product family	STV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de