

Dust filter

STF G2-1/2-IG N

Part no.: 10.07.01.00010

<https://www.schmalz.com/10.07.01.00010>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF G2-1/2-IG N

Dust filter




Connection: G2-1/2"-F

Shape: Steel housing

Nominal flow rate: 360 m³/h

Filter pore size: 3 µm

Design Data



Attribute	Value
B1	123 mm
D	200 mm
G1	G2-1/2"-F
G2	G2-1/2"-F
L	250 mm
L1	490 mm
L2	12 mm

Technical Data

Attribute	Value
Connection	G2-1/2"-F
Nominal flow rate	360 m ³ /h
Nominal flow rate	6000 l/min
Max. vacuum	-950 mbar
Filter pore size	3 µm
Weight	4.30 kg
Product family	VF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Dust filter

STF G2-1/2-IG N

Part no.:10.07.01.00010

<https://www.schmalz.com/10.07.01.00010>

Spare parts



FILT-EINS 3 150x222 PAP STF-2-1/2-IG

Part no.:10.07.01.00020

Filter pore size: 3 µm

External diameter D: 150 mm

Length L: 222 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 2-1/2-IG



FILT-EINS 3 150x222 PAP STF-2-1/2-IG

Part no.:10.07.01.00020

Filter pore size: 3 µm

External diameter D: 150 mm

Length L: 222 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 2-1/2-IG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de