

Suspension, fixable

FST-C 100-HD1

Part no...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Suspension Clampable FST-C > FST-C 100-HD1

Suspension with height compensation and pneumat. clamping heavy-duty



Shape mounting elements: Heavy Duty 1 spring plunger

Spring stroke Z: 100 mm


Weight: 9 kg

Length L: 170 mm

Width B: 170 mm

Height H: 50 mm

Design Data



Attribute	Value
B	170 mm
B1	410 mm
B2	45 mm
H	50 mm
H1	89.40 mm
L	170 mm
L1	250 mm
L2	220 mm
Z (Stroke)	100 mm

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suspension, fixable

FST-C 100-HD1

Part no...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>



EMV 5 24V-DC 3/2 NO

Part no...:10.05.01.00068

Nominal size: 5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open

Connecting thread: G1/4"-F

Pressure range (operating pressure): bar

Power consumption DC: 8 W



MOD-FLAN 157x120 SBX-C

Part no...:10.01.20.01274

Weight: 1.77 kg

Length L: 157 mm

Width B: 120 mm

Height H: 60 mm

Construction use: Large-area vacuum gripper-C



MOD-FLAN 157x120 SBX-C

Part no...:10.01.20.01275

Weight: 1.77 kg

Length L: 157 mm

Width B: 120 mm

Height H: 60 mm

Construction use: Large-area vacuum gripper-C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suspension, fixable

FST-C 100-HD1

Part no...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>



PROP-VENT 24V-DC DC

Part no...:10.05.05.00104

Thread G1: G1/8"-F

Voltage: 24V - DC

Current type: Direct current



STV-GE G1/4-AG 6

Part no...:10.08.02.00205

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.2 mm

Length L: 15.2 mm