

Bellows suction cup f SCG(S)-gripper

BCG 40 SI-MD-55 SC095


Part no...:10.01.06.04560

<https://www.schmalz.com/10.01.06.04560>




Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > BCG 40 SI-MD-55 SC095

Bellows suction cup (round) for high volumeflow with optimum adaption to uneven surfaces



Size: 40
Suction cup material: Silicone SI metal detectable
Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d2	26 mm
Dmax(S)	42 mm
Ds	39.40 mm
H	19.50 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55 Shore A
Weight	8 g