

Magnetic gripper


SGM-HP 40 G1/4-IG

Part no.: 10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Magnetic Grippers SGM-HP/-HT > SGM-HP 40 G1/4-IG

Magnetic gripper for handling metal sheets with holes




Socket: G1/4"-F

Pressure range (operating pressure): 2.5 ... 6.0 bar

Holding force max. friction ring: 235 N

Holding force max. without friction ring: 320 N

Design Data



Attribute	Value
B	40.65 mm
B2	24.20 mm
D	40 mm
G1	G1/4"-F
G2	G1/8"-F
G4	M4-F
G5	M4-F
H	99.40 mm
H2	15.70 mm
L2	32 mm
LG1	9 mm
LG2	6 mm
LG4	5 mm
X1	74 mm
Y1	12 mm

Note: Contact surface of grippers without friction ring (stadium-shaped) corresponds to dimension D x B2; with friction ring (round) dimension D

Technical Data

Attribute	Value
Holding force max. without friction ring	320 N

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HP 40 G1/4-IG

Part no...:10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>

Holding force max. friction ring	235 N
Sheet thickness opt f. holding force max.	4 mm
Holding force 2mm-sheet without friction ring	290 N
Holding force 2mm-sheet friction ring	210 N
Remaining force	0.30 N
Pressure range (operating pressure)	2.5 ... 6.0 bar
Installation position	BEL
Control valve	Bistable
Operating temperature	5 ... 70 °C
Weight	415 g
Product family	SGM-HP-HT

Note: The specified holding forces are static values under optimal conditions (primarily depending on material and surface characteristics). For system designs, a safety factor of $S = 3$ must be applied. Holding forces SGM-HT-HP at 20 °C; can be used for workpiece temperatures up to 350 °C (depending on process conditions), the influence of temperature can reduce holding forces by up to 30%

Accessories



HTS-A2 SGM-HP 30/40 OP

Part no...:10.01.17.00567

Connection 1: Bolt with slot Ø19mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40



HTS-A3 SGM-HP 30/40 OP

Part no...:10.01.17.00557

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HP 40 G1/4-IG

Part no...:10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>




HTS-A5 SGM-HP 30/40 OP

Part no...:10.01.17.00563

Connection 1: Ball head 32 mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40



HPS-SGM-HP 2M8 30/40 OP

Part no...:10.01.17.00651

Construction use: Magnetic gripper SGM-HP

Connection 1: 2x screws M8

Size: 30/40

Shape: One-piece



SCHUTZ SGM-40 ST

Part no...:10.01.17.00521

Construction use: Magnetic gripper

Size: 40

Material: Steel

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HP 40 G1/4-IG

Part no...:10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>



NAEH-SCHA SMAGN-PNP S051

Part no...:10.01.17.00199

Construction shape vacuum switch: Magn. cylind. sensor - PNP

Voltage DC: 15-30V DC

Electrical connection: Male connect M12, 4 pol



NAEH-SCHA SMAGN-NPN S050

Part no...:10.01.17.00215

Construction shape vacuum switch: Magn. cylind. sensor - NPN

Voltage DC: 12-30V DC

Electrical connection: Male connect M12, 4 pol



ADP-E-TRI 30/40 SET

Part no...:10.01.17.00421

Shape: Triangle

Workpiece diameter (min): 10 mm

Workpiece diameter (max): 20 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HP 40 G1/4-IG

Part no...:10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>



ADP-E-UNI 30/40 SET

Part no...:10.01.17.00423

Shape: rectangular



STV-GE G1/8-AG 6

Part no...:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm



STV-W G1/8-AG 6

Part no...:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20.1 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HP 40 G1/4-IG

Part no.:10.01.17.00304

<https://www.schmalz.com/10.01.17.00304>



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Spare parts



REIB-RING SGM 40 PU-55

Part no.:10.01.17.00373

Construction use: Magnetic gripper

Size: 40

External diameter D: 40 mm

Internal diameter d: 32 mm