

## Mounting plate

BEF-PL 38x15x11.5 G1/4-IG SNG

Part no...:10.01.29.00403

<https://www.schmalz.com/10.01.29.00403>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Needle Grippers > Accessories Needle Grippers SNG-V > BEF-PL 38x15x11.5 G1/4-IG SNG

### Mounting plate



Pressure range (operating pressure): bar

Length L: 38 mm


Width B: 15 mm

Height H: 11.5 mm

Thread G1: G1/4"-F

Construction use: Needle gripper

### Design Data



| Attribute | Value    |
|-----------|----------|
| B         | 15 mm    |
| d         | 5.50 mm  |
| G1        | G1/4"-F  |
| H         | 11.50 mm |
| H2        | 5 mm     |
| L         | 38 mm    |
| L2        | 20 mm    |
| LG1       | 11.50 mm |
| X1        | 29 mm    |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 14.20 g |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)