

## Flange plate (round)

FLAN-PL 63x11.5-UNI

Part no.:10.01.30.00017

<https://www.schmalz.com/10.01.30.00017>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories STGG > FLAN-PL 63x11.5-UNI

### Flange plate (round)




External diameter D: 63 mm

Length L: 11.5 mm

Size: UNI

### Design Data



| Attribute | Value    |
|-----------|----------|
| d         | 25 mm    |
| D3        | 55 mm    |
| D         | 63 mm    |
| Dmk       | 46 mm    |
| G2        | M4-F     |
| L         | 11.50 mm |
| L3        | 6.50 mm  |

### Technical Data

| Attribute                           | Value |
|-------------------------------------|-------|
| Pressure range (operating pressure) | bar   |
| Weight                              | 62 g  |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)