

Flange plate (round)

FLAN-PL 55x7.5-EL1

Part no...:10.01.30.00208

<https://www.schmalz.com/10.01.30.00208>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories STGG > FLAN-PL 55x7.5-EL1

Flange plate (round)




External diameter D: 55 mm

Length L: 7.5 mm

Size: EL1

Design Data



Attribute	Value
d	10 mm
d1	4.30 mm
D2	16 mm
D	55 mm
Dmk	28 mm
D mk1	46 mm
G2	M4-F
L	7.50 mm
L1	9.50 mm
L2	2 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Weight	34.90 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de