

Solenoid valve pressure

EMV 1.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00288

<https://www.schmalz.com/10.05.01.00288>

Home > Accessories STGG > EMV 1.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV for direct control of compressed air



Nominal size: 1.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally closed

Connecting thread: M5-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol

Design Data



Attribute

Value

B1 26.60 mm

B2 8.10 mm

d 4 mm

G1 M5-M

G2 M5-F

L 43.10 mm

L1 46.50 mm

Technical Data

Attribute

Value

Nominal size 1.50 mm

Control valve Normally closed

Nominal flow rate 45 l/min

Nominal flow rate 2.70 m³/h

Voltage DC 24V - DC

Weight 0.07 kg

Product family EMV

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Solenoid valve pressure

EMV 1.5 24V-DC 3/2 NC K-2P

Part no...:10.05.01.00288

<https://www.schmalz.com/10.05.01.00288>
