

Vacuum/pressure switch pneumatic

VS-V-PM-NC

Part no.: 10.06.02.00455

<https://www.schmalz.com/10.06.02.00455>

Home > Vacuum Technology for Automation > Vacuum Components > Switches and System Monitoring > Mechanic Vacuum Switches > Vacuum Switches VS-V-PM/EM-ST > VS-V-PM-NC

Vacuum switch, pneumatic, with pneumatic output signal




Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: Normally closed

Hysteresis: Fixed: approx. 40 mbar

Design Data



Attribute	Value
B	19.80 mm
d	4 mm
d3	4.20 mm
G2	M5-F
H	40 mm
L	58 mm
X1	41 mm

Technical Data

Attribute	Value
Overpressure resistance	6 bar
Repeatability	± 3% of full-scale value
Hysteresis	Fixed: approx. 40 mbar
Construction shape vacuum switch	Normally closed
Weight	33 g
Product family	VS-V-PM / EM-ST

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de