

Basic Ejector

SBP 07 S01 SDA

Part no.:10.02.01.00564

<https://www.schmalz.com/10.02.01.00564>

[Home](#) > [Vacuum Technology for Automation](#) > [Vacuum Components](#) > [Vacuum Generators](#) > [Basic Ejectors](#) > [Basic Ejectors SBP](#) > [SBP 07 S01 SDA](#)

Basic ejector for universal use



Nozzle diameter: 0.7 mm

Add. function: Axial silencer

Degree of evacuation: 85 %


Connection: Hose D4(1)-D4(2)

Pressure optimal: 4.5 bar

Suction rate (max.): 16 l/min

Air consumption suction: 22 l/min

Design Data



Attribute	Value
B	10 mm
d	4.20 mm
d1	4 mm
d2	4 mm
D	9 mm
H	26 mm
H1	28 mm
H2	5.20 mm
H3	12 mm
L	45 mm
L1	71 mm
L2	18 mm
L3	2 mm
L4	12.50 mm
X1	20 mm

Technical Data

Attribute	Value
Nozzle diameter	0.70 mm
Degree of evacuation	85 %
Suction rate (max.)	1 m³/h

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Basic Ejector

SBP 07 S01 SDA

Part no.:10.02.01.00564

<https://www.schmalz.com/10.02.01.00564>

Suction rate (max.)	16 l/min
Air consumption suction	1.30 m³/h
Air consumption suction	22 l/min
Sound level free	65 dB(A)
Sound level suction	59 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.50 bar
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	2 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5 ... 87.0
Suction rate (max.)	0.57 cfm
Air consumption suction	0.78 cfm
Weight	7.50 g
Product family	SBP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



BEF-PL 110x44.5x3 SBP

Part no.:10.02.01.00511

Length L: 110 mm

Width B: 44.5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Basic Ejector

SBP 07 S01 SDA

Part no...:10.02.01.00564

<https://www.schmalz.com/10.02.01.00564>



SET SBP M4-IG

Part no...:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



VFI CN6/4 50

Part no...:10.07.01.00241

Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm



VFI 4/2 50

Part no...:10.07.01.00329

Connection: Hose 4/2

Filter pore size: 50 µm

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Basic Ejector

SBP 07 S01 SDA

Part no...:10.02.01.00564

<https://www.schmalz.com/10.02.01.00564>



SD M5-AG 9x24

Part no...:10.02.01.00539

Thread G1: M5-M

External diameter D: 9 mm

Length L: 24 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de