

Basic Ejector

SBP 15 S02 SDA

Part no.:10.02.01.00566

<https://www.schmalz.com/10.02.01.00566>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP > SBP 15 S02 SDA

Basic ejector for universal use



- Nozzle diameter: 1.5 mm
- Add. function: Axial silencer
- Degree of evacuation: 85 %
- Connection: Hose D6(1)-D8(2)
- Pressure optimal: 4.5 bar
- Suction rate (max.): 71 l/min
- Air consumption suction: 105 l/min

Design Data



Attribute	Value
B	15 mm
d	4.20 mm
d1	6 mm
d2	8 mm
D	14 mm
H	34 mm
H1	40 mm
H2	5.20 mm
H3	14 mm
L	51.50 mm
L1	97 mm
L2	22 mm
L3	5.50 mm
L4	12.50 mm
X1	20 mm

Technical Data

Attribute	Value
Nozzle diameter	1.50 mm
Degree of evacuation	85 %
Suction rate (max.)	4.30 m³/h

Basic Ejector

SBP 15 S02 SDA

Part no.:10.02.01.00566

<https://www.schmalz.com/10.02.01.00566>

Suction rate (max.)	71 l/min
Air consumption suction	6.30 m³/h
Air consumption suction	105 l/min
Sound level free	72 dB(A)
Sound level suction	65 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.50 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5 ... 87.0
Suction rate (max.)	2.51 cfm
Air consumption suction	3.71 cfm
Weight	22 g
Product family	SBP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



BEF-PL 110x44.5x3 SBP

Part no.:10.02.01.00511

Length L: 110 mm

Width B: 44.5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Basic Ejector

SBP 15 S02 SDA

Part no...:10.02.01.00566

<https://www.schmalz.com/10.02.01.00566>



SET SBP M4-IG

Part no...:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



VFT G1/4-IG 80

Part no...:10.07.01.00119

Connection: G1/4"-F

Shape: Short filter insert

Nominal flow rate: 110 l/min

Nominal flow rate: 6.6 m³/h

Filter pore size: 80 µm

Spare parts



SD G1/8-AG 14x40

Part no...:10.02.01.00540

Thread G1: G1/8"-M

External diameter D: 14 mm

Length L: 40 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de