

Tooling-System-Schmalz-Ejektor


SEAC 10 RP VS-T L

Part no.:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Decentralized Ejectors > Ejectors With Blow Off
System SEAC RP > SEAC 10 RP VS-T L

Tooling-System-Schmalz-Ejektor



Nozzle diameter: 1 mm


Function: pneumatic air-saving function

Add. function: electronic vacuum switch

construction shape compact ejectors: Version left

Pressure range (operating pressure): 4.0 ... 6.0 bar

Design Data



Attribute	Value
B	44.50 mm
B3	14.20 mm
d	4.30 mm
d1	13.80 mm
D	27 mm
G1	G1/8"-F
G3	M8-M
G4	G1/8"-F
H	38.30 mm
H1	39.80 mm
H2	29.30 mm
L	52 mm
L1	88.10 mm
L2	29.50 mm
L3	8 mm
L4	22 mm
X1	28 mm

Technical Data

Attribute	Value
-----------	-------

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no.:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>

Nozzle diameter	1 mm
Degree of evacuation	85 %
Suction rate (max.)	36 l/min
Suction rate (max.)	2.10 m³/h
Air consumption suction	65 l/min
Air consumption suction	3.90 m³/h
Max. air consumption blow off	92 l/min
Pressure range (operating pressure)	4.0 ... 6.0 bar
Weight	180 g
Pressure range (operating pressure)	58.0 ... 87.0
Suction rate (max.)	1.27 cfm
Air consumption suction	2.30 cfm
Air consumption blow off	3.18 cfm
Max. vacuum	25.10 inHg
Product family	SEAC-RP

Note: Air consumption: At optimal operating pressure (4,5 bar)

Accessories



ASK B-M8-4 5000 K-4P

Part no.:10.06.02.00031

Electrical connection: Fem connect M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>



ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-S

Part no...:10.02.02.03483

Length L: 45.5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-L

Part no...:10.02.02.03484

Length L: 45.5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



ADP-EJ 38x20x11-G1/4-IG SEAC

Part no...:10.02.02.04067

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>



ADP-EJ 38x20x11-G1/8-IG SEAC

Part no...:10.02.02.04068

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/8"-F

Construction use: Compact ejectors SEAC

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de