

Vacuum blower

SB 160 115 0.9 IE3-TYP2

Part no.:10.04.01.00068

<https://www.schmalz.com/10.04.01.00068>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB > SB 160 115 0.9 IE3-TYP2

Vacuum Blower for high suction rate



Suction rate (60 Hz): 160 m³/h

Vacuum (60 Hz): 115 mbar

Rated power 60 Hz: 0.9 kW

Voltage at 60Hz: YY230/Y460V ±10%


Construction: IE3:US/CAN

Permission: UL/CSA

Permission: UL/CSA

Weight: 21.7 kg

Design Data



Attribute	Value
B	264 mm
B1	295 mm
d	10.20 mm
D2	40 mm
G1	G1-1/2"-F
H	309 mm
L	387 mm
X1	240 mm
Y1	240 mm

Technical Data

Attribute	Value
Suction rate (60 Hz)	160 m³/h
Vacuum (60 Hz)	115 mbar
Protection type IP	IP 55
Rated power 60 Hz	0.90 kW
Voltage at 60Hz	YY230/Y460V ±10%
Noise level (60 Hz)	61.70 dB(A)
Weight	21.70 kg
Construction	IE3-TYP2

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum blower

SB 160 115 0.9 IE3-TYP2

Part no.:10.04.01.00068

<https://www.schmalz.com/10.04.01.00068>

Permission	UL/CSA
Construction	IE3:US/CAN
Product family	SB

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



STF 40 P 4.5 SSD

Part no.:10.07.01.00398

Connection: Ø40mm

Shape: Piclon housing

Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD