

Vacuum pump

EVE-TR-M 2.3 24V-DC

Part no.:10.03.01.00192

<https://www.schmalz.com/10.03.01.00192>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR-M 2.3 24V-DC

Oil-free pump with constant suction rate, robust, requires little maintenance




Sound level at 50 Hz: 72 dB(A)

Weight: 2.4 kg

Max. vacuum: -780 mbar

Design Data



Attribute	Value
B	82 mm
B2	11 mm
G2	G1/8"-F
G3	G1/8"-F
G5	M4-F
H	123 mm
L	154 mm
X1	28 mm
Y1	60 mm

Technical Data

Attribute	Value
Max. vacuum	-780 mbar
Suction rate at DC	2.04 m³/h
Voltage	24V - DC
Sound level at 50 Hz	72 dB(A)
Weight	2.40 kg
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de



Vacuum pump

EVE-TR-M 2.3 24V-DC

Part no.:10.03.01.00192

<https://www.schmalz.com/10.03.01.00192>

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 |
customercenter@schmalz.de