

Bellows suction cup (oval)

SAOB 60x30 HT2-65 G3/8-IG

Part no.:10.01.06.02441

<https://www.schmalz.com/10.01.06.02441>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Oval) > Bellows Suction Cups SAOB HT2 (Oval, 1.5 Folds) > SAOB 60x30 HT2-65 G3/8-IG

Bellows suction cup (oval) for best dynamics



Dimensions (LxB): 60 x 30


Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
B1	31 mm
Bmax(S)	33 mm
Bs	30.60 mm
dn	6 mm
G1	G3/8"-F
H	35 mm
L1	55.70 mm
LG1	9 mm
Lmax(S)	63 mm
Ls	60.60 mm
SW1	22 mm
Z (Stroke)	7 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	38 N
Pull-off force	55 N
Lateral force	56 N
Volume	9.60 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	4 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup (oval)

SAOB 60x30 HT2-65 G3/8-IG

Part no...:10.01.06.02441

<https://www.schmalz.com/10.01.06.02441>

Dimensions (LxB)	60 x 30
Number of folds	1.50
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	56.70 g
Product family	SAOB