

Suction plate (round)

SPU 210 NBR-55 G1/2-IG B

Part no.:10.01.01.10552

<https://www.schmalz.com/10.01.01.10552>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Wood > Suction Plates
SPU > SPU 210 NBR-55 G1/2-IG B

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 210

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Connection: G1/2"-F

Design Data



Attribute	Value
d	34 mm
d2	159 mm
d3	138 mm
Dmax(S)	220 mm
Ds	210 mm
G1	G1/2"-F
G2	G1/4"-F
H	29 mm
H1	29.50 mm
L2	36.50 mm
LG1	13.50 mm
LG2	15 mm
Z (Stroke)	9.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1870 N
Suction force d2	1190 N
Volume	321 cm ³

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 210 NBR-55 G1/2-IG B

Part no.:10.01.01.10552

<https://www.schmalz.com/10.01.01.10552>

Curve radius (min) (convex)	750 mm
Hose diameter (rec.) d	12 mm
Size	210
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	860 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 210

Part no.:10.01.01.12439

Size: 210

Clamping range: 210.0 ... 220.0 mm

Temperature resistance: 80 °C

Spare parts



DR-SPU 210 NBR-55 B

Part no.:10.01.01.10502

Size: 210

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 210 NBR-55 G1/2-IG B

Part no.:10.01.01.10552

<https://www.schmalz.com/10.01.01.10552>
