

Flat suction cup (oval)

SAOF 50x16 NBR-45 G3/8-IG

Part no.:10.01.05.00553

<https://www.schmalz.com/10.01.05.00553>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 50x16 NBR-45 G3/8-IG

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 50x16

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
Bmax(S)	18 mm
Bs	14.60 mm
dn	6 mm
G1	G3/8"-F
H	34 mm
LG1	9 mm
Lmax(S)	52 mm
Ls	48.60 mm
SW1	22 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	31 N
Lateral force	24 N
Lateral force (oily surface)	12 N
Volume	2.27 cm ³
Curve radius (min) (convex)	7.50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SAOF 50x16 NBR-45 G3/8-IG

Part no.:10.01.05.00553

<https://www.schmalz.com/10.01.05.00553>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45 Shore A
Weight	45 g
Product family	SAOF
Dimensions (LxB)	50x16

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m